PHILIPS

Bulb

LED


2.3W-40W

E27

Cool White

Light that's **easy** on your eyes

EyeComfort*



8719514343740



Clear LED candle bulbs add a sparkle to your home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

Choose for a sustainable solution

- Better for your wallet and your planet
- Long life bulb - Lasts up to 50 years

Designed to be seen, looks good on and off

- Classic glass LED

Highlights

Saving up to 90% energy
LED technology saves up to 90% energy compared to your standard bulb. It therefore pays for itself and saves you money year after year. It also helps protect the environment.

Long life bulb - Lasts up to 50 years
With a lifetime of up to 50,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 50 years.

Glass Clear Design
The look you love, the performance you expect. Classic clear glass designs that replicate the beautiful sparkling light of traditional bulbs, for a perfect fit throughout your home.

Specifications

Bulb characteristics
- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27

Bulb dimensions
- Height: 10.5 cm
- Width: 6 cm

Durability
- Nominal lifetime: 50,000 hour(s)
- Number of switch cycles: 500,000

Light characteristics
- Color rendering index (CRI): 80
- Color temperature: 4000 K
- Nominal luminous flux: 485 lm
- Warm-up time to 60% light: instant full light
- Color Code: 840 | CCT of 4000K

Miscellaneous
- EyeComfort: Yes

Other characteristics
- Efficacy: 210 lm/W

Packaging information
- EAN: 8719514343740
- EOC: 871951434374000
- Product title: LED CLA 40W A60 E27 4000K CL EELA SRT4

Power consumption
- Power factor: 0.4
- Voltage: 220-240 V
- Wattage: 2.3 W
- Wattage equivalent: 40 W
- Energy Efficiency Label (EEL): A

Product dimensions and weight
- Length: 10.5 cm

Technical specifications
- Frequency: 50-60 Hz
- EPREL Registration Number: 1370028
- Flux measurement reference: Sphere

The bulb
- Color consistency: 6

Issue date: 2023-12-07
Version: 0.171

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com