

PHILIPS

Bulb

LED

4 W-60 W

E27

White

Light that's **easy** on your eyes  EyeComfort*



*Designed for the comfort of your eyes. See below for more information.

8719514343788



Clear LED candle bulbs add a sparkle to your home

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your clear incandescent bulbs.

Choose for a sustainable solution

- Better for your wallet and your planet
- Long life bulb – Lasts up to 45 years

Designed to be seen, looks good on and off

- Classic glass LED

Highlights

Energy savings of up to 90%

LED technology provides energy savings of up to 90% compared with your standard bulb. It therefore pays for itself and saves you money year after year. It also helps to protect the environment.

Long life bulb – Lasts up to 45 years

With a lifetime of up to 45,000 hours, you can reduce the hassle of frequently replacing your light bulbs and enjoy a perfect lighting solution for over 45 years.

Glass Clear Design

The look you love, the performance you expect. Classic clear glass designs that replicate the beautiful sparkling light of traditional bulbs, for a perfect fit throughout your home.

Specifications

Characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non-directional bulb
- Socket: E27
- Technology: LED
- Type of glass: Clear

Lamp dimensions

- Height: 10.5 cm
- Weight: 0.036 kg
- Width: 6 cm

Durability

- Average life (at 2.7 hrs/day): 51 a
- Lumen maintenance factor: 70%
- Nominal lifetime: 50,000 h
- Number of switch cycles: 500,000

Light characteristics

- Colour consistency: 6SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 3000 K
- Light Colour Category: White
- Nominal luminous flux: 840 lm
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Colour Code: 830 | CCT of 3000K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 45 mA
- Efficacy: 210 lm/W

Packaging information

- EAN: 8719514343788
- EOC: 871951434378800
- Product title: LED CLA 60W A60 E27 3000K CL EELA SRT4

Power consumption

- Power factor: 0.4
- Voltage: 220–240 V
- Wattage: 4 W
- Wattage equivalent: 60 W
- Energy Efficiency Class: A

Product dimensions and weight

- Length: 10.5 cm

Rated values

- Rated lifetime: 50,000 h
- Rated luminous flux: 840 lm
- Rated power: 4 W

Technical specifications

- Frequency: 50–60 Hz

The bulb

- Colour consistency: 6

Packaging dimensions and weight

- EAN/UPC – product: 8719514343788
- Net weight: 0.030 kg
- Gross weight: 0.054 kg
- Height: 14.600 cm
- Length: 6.500 cm
- Width: 6.300 cm
- Material number (12NC): 929003066701



Issue date: 2021-10-06
Version: 0.167

© 2021 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com