

# PHILIPS

Bulb

LED

4 W-60 W

E27

Cool White

Light that's **easy**  
on your eyes 



\*Designed for the comfort of your eyes.  
See below for more information.

8719514343801



## Clear LED candle bulbs add a sparkle to your home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

### Choose for a sustainable solution

- Better for your wallet and your planet
- Long life bulb – Lasts up to 45 years

### Designed to be seen, looks good on and off

- Classic glass LED

# Highlights

## Energy savings of up to 90%

LED technology provides energy savings of up to 90% compared with your standard bulb. It therefore pays for itself and saves you money year after year. It also helps to protect the environment.

## Long life bulb – Lasts up to 45 years

With a lifetime of up to 45,000 hours, you can reduce the hassle of frequently replacing your light bulbs and enjoy a perfect lighting solution for over 45 years.

## Glass Clear Design

The look you love, the performance you expect. Classic clear glass designs that replicate the beautiful sparkling light of traditional bulbs, for a perfect fit throughout your home.

# Specifications

## Characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non-directional bulb
- Socket: E27
- Technology: LED
- Type of glass: Clear

## Lamp dimensions

- Height: 10.5 cm
- Weight: 0.036 kg
- Width: 6 cm

## Durability

- Average life (at 2.7 hrs/day): 51 a
- Lumen maintenance factor: 70%
- Nominal lifetime: 50,000 h
- Number of switch cycles: 500,000

## Light characteristics

- Colour consistency: 6SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 4000 K
- Light Colour Category: Cool White
- Nominal luminous flux: 840 lm
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Colour Code: 840 | CCT of 4000K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 45 mA
- Efficacy: 210 lm/W

## Packaging information

- EAN: 8719514343801
- EOC: 871951434380100
- Product title: LED CLA 60W A60 E27 4000K CL EELA SRT4

## Power consumption

- Power factor: 0.4
- Voltage: 220–240 V
- Wattage: 4 W
- Wattage equivalent: 60 W
- Energy Efficiency Class: A

## Product dimensions and weight

- Length: 10.5 cm

## Rated values

- Rated lifetime: 50,000 h
- Rated luminous flux: 840 lm
- Rated power: 4 W

## Technical specifications

- Frequency: 50–60 Hz

## The bulb

- Colour consistency: 6

## Packaging dimensions and weight

- EAN/UPC – product: 8719514343801
- Net weight: 0.030 kg
- Gross weight: 0.054 kg
- Height: 14.600 cm
- Length: 6.500 cm
- Width: 6.300 cm
- Material number (12NC): 929003066801



Issue date: 2021-10-06  
Version: 0.156

© 2021 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)