

# PHILIPS

Spot (Dimmable)

LED

7.5W-50W

GU5.3

Warm White

Dimming

8719514357631



## Durable LED accent lighting with a focused bright beam

This Philips LED spot provides a dimmable, focused bright beam, an exceptionally long life, and significant energy savings. This spot is the perfect long-lasting replacement for 50W spots with a GU10 cap.

### High quality light

- Cool, energizing light

### Choose for a sustainable solution

- Saves up to 80% Energy

### Create the right light for your home

- Perfect for accent lighting and general purpose lighting

# Highlights

## 3500K [LED Lamps]



This bulb has a color temperature of 3500K providing you with a cool, energizing light, perfect for creating an inviting ambiance to host friends or wind down with a book.

## Saves up to 80% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

## 60° beam - spot



Modern lighting with a familiar extra wide angle light output (60 degrees), this LED spot is suitable for both accent lighting and general purpose lighting. It can be used in recessed cans and track light fixtures, and is ideal for use in kitchens, kitchen island lighting, living rooms and dining rooms.

# Specifications

## Characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Directional spot
- Socket: GU5.3
- Technology: LED

## Bulb dimensions

- Height: 4.55 cm
- Weight: 0.048 kg
- Width: 5.05 cm

## Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 25,000 h
- Number of switch cycles: 50,000

## Light characteristics

- Beam angle: 60 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 90
- Color temperature: 3000 K
- Light Color Category: Warm White
- Nominal luminous flux: 630 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 930 | CCT of 3000K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 660 mA
- Efficacy: 94 lm/W

## Packaging information

- EAN: 8719514357631
- EOC: 871951435763100
- Product title: LEDspots 7.5-50W MR16 930 DIM 60D 1PF/10

#### Power consumption

- Power factor: 0.7
- Voltage: 12V AC electronic V
- Wattage: 7.5 W
- Wattage equivalent: 50 W

#### Product dimensions & weight

- Length: 4.55 cm

#### Rated values

- Rated beam angle: 60 degree(s)
- Rated lifetime: 25,000 h
- Rated luminous flux: 630 lumen
- Rated peak intensity: 800 cd
- Rated power: 7.5 W

#### Technical specifications

- Frequency: - Hz

#### Packaging dimensions & weight

- EAN/UPC - product: 8719514357631
- Net weight: 0.060 kg
- Gross weight: 0.068 kg
- Height: 8.200 cm
- Length: 4.500 cm
- Width: 4.500 cm
- Material number (12NC):  
929002493609



Issue date: 2021-09-15  
Version: 0.26

© 2021 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)