

# PHILIPS

Spot


LED

7.5W-60W

R7S

Warm White

8719514372931



## Durable LED light with a 300 degree light beam

This innovative Linear LED is the perfect replacement for halogen R7S lamps, while far surpassing them in terms of energy efficiency.

### High quality light

- Cool, energizing light

### Choose a simple replacement for your old bulbs

- Similar shape and size as halogen spot
- Similar shape and size as halogen linear

# Highlights

## 3500K [LED Lamps]



This bulb has a color temperature of 3500K providing you with a cool, energizing light, perfect for creating an inviting ambiance to host friends or wind down with a book.

## Replaces halogen reflector



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, LED capsule. The perfect sustainable replacement for traditional halogen spots.

## Replaces linear halogen



With its beautifully shaped design and familiar dimensions, this standard modern lighting, LED linear is the perfect sustainable replacement for traditional halogen linears.

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional reflector
- Socket: R7s
- Bulb Finish: Clear
- Bulb Material: Plastic

## Bulb dimensions

- Height: 7.8 cm
- Width: 2.9 cm

## Durability

- Nominal lifetime: 15,000 h
- Number of switch cycles: 50,000
- Ambient temperature range: -20 to +45 °C

## Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Nominal luminous flux: 950 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 830 | CCT of 3000K
- Correlated Color Temperature (Nom): 3000 K
- Luminous Efficacy (rated) (Nom): 126 lm/W
- Luminous Flux: 950 lm

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Efficacy: 126 lm/W
- EU RoHS compliant: Yes

## Packaging information

- EAN: 8719514372931
- EOC: 871951437293100
- Product title: LED 7.5-60W R7S 78mm 830 ND 1pk AU

## Power

- Power Factor (Fraction): 0.5

## Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 7.5 W
- Wattage equivalent: 60 W
- Power Consumption: 7.5 W

## Product dimensions and weight

- Length: 7.8 cm

## Rated values

- Rated lifetime: 15,000 h

#### Technical specifications

- Frequency: 50-60 Hz
- Dimmable: No
- Cap-Base: R7s

#### Packaging dimensions & weight

- EAN/UPC - product: 8719514372931
- Net weight: 0.05 kg
- Gross weight: 0.06 kg
- Height: 8 cm
- Length: 3 cm
- Width: 4.2 cm
- Material number (12NC):  
929001339079



Issue date: 2024-02-06  
Version: 0.21

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)