

PHILIPS

Spot (Dimmable)

LED


17.5W-150W

R7S

Warm White

Dimming

8719514372979



Dimmable linear LED light with a 300 degree beam

This innovative Linear LED is the perfect replacement for halogen R7S lamps, while far surpassing them in terms of energy efficiency.

High quality light

- Cool, energizing light

Choose a simple replacement for your old bulbs

- Similar shape and size as halogen spot
- Similar shape and size as halogen linear

Highlights

3500K [LED Lamps]



This bulb has a color temperature of 3500K providing you with a cool, energizing light, perfect for creating an inviting ambiance to host friends or wind down with a book.

Replaces halogen reflector



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, LED capsule. The perfect sustainable replacement for traditional halogen spots.

Replaces linear halogen



With its beautifully shaped design and familiar dimensions, this standard modern lighting, LED linear is the perfect sustainable replacement for traditional halogen linears.

Specifications

Characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Non directional reflector
- Socket: R7S
- Technology: LED

Bulb dimensions

- Height: 11.8 cm
- Weight: 0.16 kg
- Width: 4.2 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 h
- Number of switch cycles: 50,000

Light characteristics

- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Light Color Category: Warm White
- Nominal luminous flux: 2460 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 830 | CCT of 3000K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 90 mA
- Efficacy: 140 lm/W

Packaging information

- EAN: 8719514372979
- EOC: 871951437297900
- Product title: LED 17.5-150W R7S 118mm 830 D 1pk AU

Power consumption

- Power factor: 0.9
- Voltage: 220-240 V
- Wattage: 17.5 W
- Wattage equivalent: 150 W

Product dimensions & weight

- Length: 11.8 cm

Rated values

- Rated lifetime: 15,000 h
- Rated luminous flux: 2460 lumen
- Rated power: 17.5 W

Technical specifications

- Frequency: 50-60 Hz

Packaging dimensions & weight

- EAN/UPC - product: 8719514372979
- Net weight: 0.095 kg
- Gross weight: 0.104 kg
- Height: 12.000 cm
- Length: 3.000 cm
- Width: 4.200 cm
- Material number (12NC): 929002016679



Issue date: 2021-07-05
Version: 0.16

© 2021 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com