

PHILIPS

Candle & Lustre
(Dimmable)

LED

3.5W-40(GLS 49, CFL 8,
halogen 33)W

E14

Warm White

Dimming

8719514377295



Experience dimmable, warm white LED light

Philips LED clear candles provide a beautiful, sparkling light effect and an exceptionally long life. Beautiful both switched on and off, this light bulb is the perfect match for chandelier fixtures with small (E14) fittings.

Choose for a sustainable solution

- Better for your wallet and your planet

Create the right light for your home

- Perfect for decorative fixtures

Highlights

Saving up to 90% energy

LED technology saves up to 90% energy compared to your standard bulb. It therefore pays for itself and saves you money year after year. It also helps protect the environment.

Perfect for decorative fixture



Modern lighting in Philips LED candles for use in decorative fixtures such as in chandeliers, ceiling fans, vanity strips, and post lights.

Specifications

Bulb characteristics

- Dimmable: Only with specific dimmers
- Intended use: Indoor
- Lamp shape: Non directional candle
- Socket: E14
- Technology: LED
- Type of glass: Clear

Bulb dimensions

- Height: 9.7 cm
- Weight: 0.013 kg
- Width: 3.5 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000

Light characteristics

- Color consistency: 6SDCM
- Color rendering index (CRI): 90
- Color temperature: 2700 K
- Light Color Category: Warm White
- Nominal luminous flux: 470 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 927 | CCT of 2700K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 24 mA
- Efficacy: 134 lm/W

Packaging information

- EAN: 8719514377295
- EOC: 871951437729500
- Product title: LEDclassic 40W B35 2700K E14 D CL AU

Power consumption

- Power factor: 0.6
- Voltage: 220-240 V
- Wattage: 3.5 W
- Wattage equivalent: 40 W

Product dimensions & weight

- Length: 9.7 cm

Rated values

- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 470 lumen
- Rated power: 3.5 W

Technical specifications

- Frequency: 50-60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 8719514377295
- Net weight: 0.014 kg
- Gross weight: 0.030 kg
- Height: 14.000 cm
- Length: 4.500 cm
- Width: 4.500 cm
- Material number (12NC): 929003012279



Issue date: 2022-06-30
Version: 0.23

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com