

# PHILIPS

## Candle & Lustre

LED

3.5W-40(GLS 49, CFL 8,  
halogen 33)W

B22

Warm White

8719514377370



## Experience dimmable, warm white LED light

Philips LED frosted candles provide a soft, diffuse light effect and an exceptionally long life. With a pure and elegant design, this light bulb is the perfect match for chandelier fixtures with small (E14) fittings.

### Choose for a sustainable solution

- Better for your wallet and your planet

### Create the right light for your home

- Perfect for decorative fixtures

# Highlights

## Saving up to 90% energy

LED technology saves up to 90% energy compared to your standard bulb. It therefore pays for itself and saves you money year after year. It also helps protect the environment.

## Perfect for decorative fixture



Modern lighting in Philips LED candles for use in decorative fixtures such as in chandeliers, ceiling fans, vanity strips, and post lights.

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional candle
- Socket: B22
- Type of glass: Frosted
- Bulb Finish: Frosted
- Bulb Material: Glass

## Bulb dimensions

- Height: 9.4 cm
- Width: 3.5 cm

## Design and finishing

- Material: Glass

## Durability

- Nominal lifetime: 15,000 h
- Number of switch cycles: 15,000
- Ambient temperature range: -20 to +45 °C

## Light characteristics

- Color rendering index (CRI): 90
- Color temperature: 2700 K
- Nominal luminous flux: 470 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 927 | CCT of 2700K
- Correlated Color Temperature (Nom): 2700 K
- Luminous Efficacy (rated) (Nom): 134 lm/W
- Luminous Flux: 470 lm

## Miscellaneous

- EyeComfort: No

## Other characteristics

- Efficacy: 134 lm/W
- EU RoHS compliant: Yes

## Packaging information

- EAN: 8719514377370
- EOC: 871951437737000
- Product title: LEDclassic 40W B35 2700K B22 ND FR AU

## Power

- Power Factor (Fraction): 0.6

## Power consumption

- Power factor: 0.6
- Voltage: 220-240 V
- Wattage: 3.5 W
- Wattage equivalent: 40 W
- Power Consumption: 3.5 W

## Product dimensions and weight

- Length: 9.4 cm

## Rated values

- Rated lifetime: 15,000 h

## Technical specifications

- Frequency: 50-60 Hz
- Dimmable: No
- Cap-Base: B22

**Packaging dimensions & weight**

- EAN/UPC - product: 8719514377370
- Net weight: 0.01 kg
- Gross weight: 0.03 kg
- Height: 14 cm
- Length: 4.5 cm
- Width: 4.5 cm
- Material number (12NC): 929003012879



Issue date: 2024-02-06  
Version: 0.20

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)