PHILIPS

Bulb (Dimmable)

LED


6W-60(GLS 72, CFL 14, halogen 50)W

E27

Warm White

Dimming

8719514385887



Experience dimmable, warm white LED light

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

Choose for a sustainable solution

- Better for your wallet and your planet

Create the right light for your home

- Perfect for general room lighting

8719514385887

Highlights

Saving up to 90% energy
LED technology saves up to 90% energy compared to your standard bulb. It therefore pays for itself and saves you money year after year. It also helps protect the environment.

Perfect for general lighting



Modern lighting with Philips LED standard bulbs for all-around illumination, perfect for general room lighting.

Specifications

Bulb characteristics
- Dimmable: Only with specific dimmers
- Intended use: Indoor
- Lamp shape: Non directional globe
- Socket: E27
- Type of glass: Clear
- Bulb Finish: Clear
- Bulb Material: Glass

Bulb dimensions
- Height: 17.8 cm
- Width: 12.4 cm

Design and finishing
- Material: Glass

Durability
- Nominal lifetime: 15,000 h
- Number of switch cycles: 20,000
- Ambient temperature range: -20 to +45 °C

Light characteristics
- Color rendering index (CRI): 90
- Color temperature: 2700 K
- Nominal luminous flux: 806 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 927 | CCT of 2700K
- Correlated Color Temperature (Nom): 2700 K
- Luminous Efficacy (rated) (Nom): 134 lm/W
- Luminous Flux: 806 lm

Other characteristics
- Efficacy: 134 lm/W
- EU RoHS compliant: Yes

Packaging information
- EAN: 8719514385887
- EOC: 871951438588700
- Product title: LEDclassic 60W E27 2700K G120 D CL AU

Power
- Power Factor (Fraction): 0.7

Power consumption
- Power factor: 0.7
- Voltage: 220-240 V
- Wattage: 6 W
- Wattage equivalent: 60 W
- Power Consumption: 6 W

Product dimensions and weight
- Length: 17.8 cm

Rated values
- Rated lifetime: 15,000 h

Technical specifications
- Frequency: 50-60 Hz
- Dimmable: Only with specific dimmers
- Cap-Base: E27

Packaging dimensions & weight

- EAN/UPC - product: 8719514385887
- Net weight: 0.17 kg
- Gross weight: 0.23 kg
- Height: 22.6 cm
- Length: 12.9 cm
- Width: 12.9 cm
- Material number (12NC): 929003059379

Issue date: 2024-02-07
Version: 0.32

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com