

# PHILIPS

6 Gang 1 Way  
Switch


Switches & Sockets

LeafStyle

White

PC

8719514389410



## Aesthetic appearance to enhance interior design

Philips provides modern design and high safety standard switches & sockets for your home

### **Safety and Durability**

- High quality PC
- IEC standard and Philips internal rule

# Highlights

## High quality PC

High quality PC for Cover and Base.

## IEC standard and Philips internal rule

Pass IEC standard and follow more strict Philips internal design rule.

# Specifications

## Design and finishing

- Color: White
- Material: PC
- Module/Gang: 6 Module
- Product Range: LeafStyle
- Minimum Installation Box Depth: 4.5 cm

## Durability

- Number of Operation Cycles: 40000

## Interactivity

- Current (A): 10AX

## Other characteristics

- Installation Type: Screwed Installation
- Indicator Type: No Indicator
- Switch Function: 1 Way

## Power

- Electrical Load Type: Resistive load, Inductive load, Capacitive load

## Power consumption

- Voltage: 250 V

## Product dimensions and weight

- Length: 14.74 cm
- Width: 9.36 cm
- Depth: 2.38 cm

## Rated values

- Fluorescent Lamp Current: 10 AX

## Service

- Warranty: 2 year(s)

## Technical specifications

- Frequency: 50-60 Hz

## Packaging dimensions and weight

- EAN/UPC - product: 8719514389410
- Net weight: 0.2 kg
- Gross weight: 0.21 kg
- Height: 3.6 cm
- Length: 14.7 cm
- Width: 9.3 cm
- Material number (12NC): 913715121508



Issue date: 2024-02-02  
Version: 0.18

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)