

PHILIPS

10 Gang 1 Way
Switch


Switches & Sockets

LeafStyle

White

PC

8719514389472



Aesthetic appearance to enhance interior design

Philips provides modern design and high safety standard switches & sockets for your home

Safety and Durability

- High quality PC
- IEC standard and Philips internal rule

Highlights

High quality PC

High quality PC for Cover and Base.

IEC standard and Philips internal rule

Pass IEC standard and follow more strict Philips internal design rule.

Specifications

Design and finishing

- Color: white
- Material: PC
- Module/Gang: 6 Module
- Product Range: LeafStyle
- Minimum Installation Box Depth: 4.5 cm

Durability

- Number of Operation Cycles: 40,000

Interactivity

- Current (A): 10AX

Other characteristics

- Installation Type: Screwed Installation
- Indicator Type: No Indicator
- Switch Function: 1 Way

Power

- Electrical Load Type: Resistive load, Inductive load, Capacitive load

Power consumption

- Voltage: 250 V

Product dimensions & weight

- Length: 14.74 cm
- Width: 9.36 cm
- Depth: 2.38 cm

Rated values

- Fluorescent Lamp Current: 10 AX

Service

- Warranty: 2 year(s)

Technical specifications

- Frequency: 50-60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 8719514389472
- Net weight: 0.230 kg
- Gross weight: 0.236 kg
- Height: 3.600 cm
- Length: 14.740 cm
- Width: 9.330 cm
- Material number (12NC): 913715121708



Issue date: 2023-01-06
Version: 0.18

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com