

# PHILIPS

Module Fan  
Regulator


Switches & Sockets

LeafStyle

White

PC

8719514389687



## Aesthetic appearance to enhance interior design

Philips provides modern design and high safety standard switches & sockets for your home

### **Safety and Durability**

- High quality PC
- Pass Philips internal rule

# Highlights

## High quality PC

High quality PC for Cover and Base.

## Pass Philips internal rule

Pass strict Philips internal design rule.

# Specifications

## Design and finishing

- Color: white
- Material: PC
- Module/Gang: 1 Module
- Product Range: LeafStyle
- Minimum Installation Box Depth: 4.5 cm

## Durability

- Number of Operation Cycles: 40,000, 10,000

## Other characteristics

- Installation Type: Wire connection

## Power consumption

- Voltage: 220 V
- Wattage: 300 W

## Product dimensions & weight

- Length: 8.74 cm
- Width: 9.34 cm
- Depth: 3.58 cm

## Service

- Warranty: 1 year(s)

## Technical specifications

- Frequency: 50-60 Hz

## Packaging dimensions and weight

- EAN/UPC - product: 8719514389687
- Net weight: 0.027 kg
- Gross weight: 0.028 kg
- Height: 6.200 cm
- Length: 3.300 cm
- Width: 3.300 cm
- Material number (12NC): 913715123708



Issue date: 2023-01-06  
Version: 0.16

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)