

# PHILIPS

Outdoor luminaires

Outdoor luminaires

SuperSlim

White

Ceiling light



8719514417991



## One fixture. Your switch. Three light settings.

Create the right mood by changing brightness. Philips' SceneSwitch LED ceiling light lets you enjoy three brightness settings that are perfect for every moment. No dimmer or additional installation is required – all you need is your existing switch.

### Light effect

- Provides a bright white light

### Sustainable light solutions

- Energy saving
- Philips offers a 5-year warranty on the LED module and driver

### Bring design into your garden

- Choose outdoor ceiling lights

### Designed for your garden

- IP54 - weather-proof (outdoor lighting)

### Designed for your living room and bedroom

- High-quality materials

# Highlights

## Superior light quality Energy saving



This Philips energy-saving lamp conserves energy compared with traditional light sources, helping you to save money on your electricity bills and do your bit for the environment.

## 5-year warranty on LED system



On top of the standard 2-year warranty for this lamp, Philips offers a 5-year warranty on the LED system, meaning the LED module and the driver in this lamp.

## Choose ceiling lights

Make the most of your outdoor space with this ceiling light, perfect for lighting your house porch or patio.

## IP54 - weather-proof (outdoor lighting)

This Philips outdoor light is especially designed for humid outdoor environments. It was tested rigorously to ensure its water resistance. The IP level is described by two figures: the first one refers to the protection level against dust, the second against water. This outdoor light is designed with IP54: it is protected against splashing water. This product is most commonly used and ideal for general outdoor use.

## High-quality materials

This lamp is sculpted from layered patterns of high-quality materials with superior finishing. This ensures a solid and long lasting product that will enhance your home for many years to come.

# Specifications

## Design and finishing

- Colour: White
- Material: Metal, Plastic

## Extra feature/accessory incl.

- Adjustable spot head: No
- Anti-rust anti-dust: Yes
- click!FIX mounting: Yes
- compatible with all dimmers: No
- Day-and-night sensor: No
- Defined light beams: Yes
- Dimmable: No
- Dimmable with remote control: No
- FFP - Frustration-Free Pack: No
- Fully weatherproof: Yes
- LED integrated: Yes
- Motion and day-and-night sensor: No
- Motion sensor: No
- Portable: No
- Remote control included: No
- Rotates freely in any direction: No
- Solar Energy: No
- Tilttable head (up-down): No
- UK plug included: No
- USB charging: No
- Warm White Light: Yes
- Waterproof: Yes
- Centrepiece: Yes

#### Light characteristics

- Colour rendering index (CRI): 80

#### Miscellaneous

- Especially designed for: Garden and Patio
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes

#### Packaging dimensions and weight

- EAN/UPC – product: 8719514417991
- Net weight: 0.47 kg
- Gross weight: 0.54 kg
- Height: 25 cm
- Length: 2.8 cm
- Width: 24.5 cm
- Material number (12NC): 929003191401

#### Product dimensions and weight

- Net weight: 0.47 kg
- Height: 2.3 cm
- Length: 25 cm
- Width: 25 cm

#### Service

- Warranty: 5 year(s)

#### Technical specifications

- Lifetime up to: 20,000 h
- Total lumen output fixture: 1500
- Light colour: 4000
- Fixture dimmable: Step Dim – Do not use with dimmer
- LED: Yes
- Energy class included light source: E
- IP code: IP54
- Class of protection: Class II
- Light source replaceable: No



Issue date: 2024-02-07  
Version: 0.195

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)