

PHILIPS

Bulb

LED

16W-/W

E27

Daylight

8719514420717



Enhanced plant growth in a beautiful white light

Philips LED Plant Grow lights not only optimize plant growth but also provide a beautiful, natural look for your plants. Full Spectrum White - the perfect color spectrum for growth and natural color.

Choose for a sustainable solution

- Long life bulb - Lasts up to 50 years

Light beyond illumination

- Enhanced color spectrum

High quality LED light that lasts for decades

- Light that shows true colors

Highlights

Long life bulb - Lasts up to 50 years

With a lifetime of up to 50,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 50 years.

Grow Light Spectrum

The perfect color spectrum to optimize plant growth while displaying your plants with a beautiful and natural look. Blue wavelengths help promote plant and vegetative growth.

Light that shows true colors



See the true colors of your clothes when you select an outfit from your wardrobe – you can pair a red dress

and red shoes with confidence and be sure the colors match perfectly.

Specifications

Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional reflector
- Socket: E27

Bulb dimensions

- Height: 13.5 cm
- Width: 12.2 cm

Durability

- Nominal lifetime: 25,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 50 degree(s)
- Color rendering index (CRI): 90
- Color temperature: 5000 K
- Nominal luminous flux: 1200 lm
- Warm-up time to 60% light: instant full light
- Color Code: 950 | CCT of 5000K

Other characteristics

- Efficacy: 75 lm/W

Packaging information

- EAN: 8719514420717
- EOC: 871951442071700
- Product title: LED Grow 16W Par38 E27 950 50D

Power consumption

- Power factor: 0.9
- Voltage: 110–240 V
- Wattage: 16 W

Product dimensions and weight

- Length: 13.5 cm

Technical specifications

- Frequency: 50–60 Hz

Packaging dimensions and weight

- EAN/UPC – product: 8719514420717
- Net weight: 0.36 kg
- Gross weight: 0.46 kg
- Height: 13.7 cm
- Length: 12.5 cm
- Width: 12.5 cm
- Material number (12NC): 929001892819



Issue date: 2024-02-02
Version: 0.56

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com