

PHILIPS

Ceiling light

Functional

Ozziet CL570

White

Dim



8719514432024



One fixture. Two light zones. Three settings.

This modern sleek slim white design looks as good off as it does on. The clean round lines of the main light are accented with a clever linear edge light. Combine the two lights together and create 3 unique light settings. The main downlight has a cool 4000k output and the linear edge accent light provides warm 2700k output. The lamp is available in 3 sizes, and therefore fits perfectly in any room of your house. The handy memory feature helps you recall your latest setting. So, if pure white design with many features is your thing, the Ozziet is the perfect ceiling light for you.

Designed for your living- and bedroom

- Perfect to relax and socialise

Match your interior

- Super slim design

Easy to experience

- Memorize your favorite mode for easy selection
- Easy installation

Light effect

- Dual zone light

Highlights

Perfect to relax and socialise

The living room is the heart of any home – a place where families gather to relax and guests socialise. Lighting for your living- and bedroom has to be flexible and easy to adjust to its different uses throughout the day. Careful placement of different light sources and playing with light layering helps create the feeling of space and to give the room a warm and welcoming feel.

Super slim design

Slim design is ideal for low-ceiling rooms, sitting flush against the surface.

Memorize your favorite mode for easy selection

Whether you prefer a warm glow for cozy evenings or a bright white light for focus, the system memorizes your favorites for easy selection.

Easy installation

No more hassle in installation. Just fix or hang securely on the wall or ceiling, and plug in, now this luminaire is ready to light on.

Dual zone light

Changing the ambiance in your room has never been easier. Philips' SceneSwitch Dual zone LED ceiling light lets you set the mood with three unique settings. The combination of main and linear edge light give you options that are perfect for your get together, concentrate and cozy moments. No dimmer or installation required – all you need is your existing switch.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Color: White
- Material: Plastic

Durability

- Number of switch cycles: 20,000

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Color consistency: 6 SDCM
- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office, Garage
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes

Other characteristics

- Lamp current: 185 mA
- Efficacy: 113 lm/W

Product dimensions and weight

- Net weight: 1 kg
- Height: 4.5 cm
- Length: 40 cm
- Width: 40 cm

Service

- Warranty: 5 year(s)

Technical specifications

- Lifetime up to: 20,000 hour(s)
- Diameter: 400 mm
- Total lumen output fixture: 2500
- Light color: 4000
- Mains power: AC 220–240
- Fixture dimmable: Step Dim – Do not use with dimmer
- LED: Yes
- Wattage bulb included: 22
- IP code: IP20
- Class of protection: Class II

Packaging dimensions and weight

- EAN/UPC – product: 8719514432024
- Net weight: 1 kg
- Gross weight: 1.44 kg
- Height: 42.5 cm
- Length: 5.4 cm
- Width: 42.5 cm
- Material number (12NC): 929003196701



Issue date: 2024-02-02
Version: 0.135

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com