

# PHILIPS

Bulb


LED

5.2W-75W

E27



8719514435674



## Bright LED lighting with excellent light quality

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your clear incandescent bulbs.

### High quality light

- Designed for the comfort of your eyes

### Choose for a sustainable solution

- Better for your wallet and your planet
- Long life bulb - Lasts up to 50 years

### Designed to be seen, looks good on and off

- Classic glass LED

# Highlights

## Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience

flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## Saving up to 90% energy

LED technology saves up to 90% energy compared to your standard bulb. It therefore pays for itself and saves you money year after year. It also helps protect the environment.

## Long life bulb - Lasts up to 50 years

With a lifetime of up to 50,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 50 years.

## Glass Clear Design

The look you love, the performance you expect. Classic clear glass designs that replicate the beautiful sparkling light of traditional bulbs, for a perfect fit throughout your home.

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Type of glass: Clear
- Bulb Finish: Clear
- Bulb Material: Glass

## Bulb dimensions

- Height: 12.7 cm
- Width: 7 cm

## Design and finishing

- Material: Glass

## Durability

- Nominal lifetime: 50,000 hour(s)
- Number of switch cycles: 50,000

## Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Nominal luminous flux: 1095 lm
- Warm-up time to 60% light: instant full light
- Color Code: 830 | CCT of 3000K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Efficacy: 210 lm/W

## Packaging information

- EAN: 8719514435674
- EOC: 871951443567400
- Product title: LED CLA 75W A70 E27 3000K CL UE SRT4

## Power consumption

- Power factor: 0.4
- Voltage: 220-240 V
- Wattage: 5.2 W
- Wattage equivalent: 75 W
- Energy Efficiency Label (EEL): A

## Product dimensions and weight

- Length: 12.7 cm

## Technical specifications

- Frequency: 50-60 Hz
- EPREL Registration Number: 1370034

## Packaging dimensions and weight

- EAN/UPC – product: 8719514435674
- Net weight: 0.05 kg
- Gross weight: 0.09 kg
- Height: 17.8 cm
- Length: 7.6 cm
- Width: 7.6 cm
- Material number (12NC): 929003480401



Issue date: 2024-02-04  
Version: 0.150

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)