

# PHILIPS

Table lamp

Functional

Bucket DSK214 40K

White

Dim

8719514443792



## Comfortable LED light that's easy on your eyes

With its robust design and optimal performance, Philips LED Performance desk light is the perfect luminaire that brings quality and brightness to any home spaces. Comfortable light that's easy on your eyes.

### Premium quality

- EyeComfort - light that's easy on the eyes

# Highlights

## Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria

including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that

way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Rectangle

## Design and finishing

- Color: White
- Material: Plastic

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 50,000

## Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Color consistency: 6 SDCM
- Color rendering index (CRI): 90
- Warm-up time to 60% light: <2

## Miscellaneous

- Especially designed for: Bedroom, Living Room, Home Office
- Style: Contemporary
- Type: Desk Lights
- EyeComfort: Yes

## Other characteristics

- Lamp current: 1400 mA
- Efficacy: 28 lm/W

## Product dimensions and weight

- Net weight: 0.5 kg
- Height: 34 cm
- Length: 31.5 cm
- Width: 11 cm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Lifetime up to: 15,000 hour(s)
- Total lumen output fixture: 200
- Light color: 3000/4000/5700
- Mains power: 5 V
- Battery type: Li-ion
- Fixture dimmable: Yes
- LED: Yes
- Wattage bulb included: 7
- IP code: IP20
- Class of protection: Class III

## Packaging dimensions and weight

- EAN/UPC – product: 8719514443792
- Net weight: 0.5 kg
- Gross weight: 0.65 kg
- Height: 34.5 cm
- Length: 11.5 cm
- Width: 18 cm
- Material number (12NC): 929003241107



Issue date: 2024-02-02  
Version: 0.256

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)