

PHILIPS

Portable

Functional

Hat DSK213 40K

White

Dim



8719514474208



The 'go anywhere' desk lamp

With its robust design and optimal performance, Philips LED Performance desk light is the perfect luminaire that brings quality and brightness to any home spaces. Comfortable light that's easy on your eyes.

Premium quality

- EyeComfort - light that's easy on the eyes

Control

- Step dimming
- Adjustable color temperature and brightness

Highlights

Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philip

s LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Adjustable color temperature and brightness

Changing color temperature and brightness allows you to change the mood and atmosphere in a room, matching the light to different kinds of activity.

Step dimming

Select from different dimming levels to create the right mood for the moment.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Rectangle

Design and finishing

- Color: white
- Material: plastic

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 50,000

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No
- Centerpiece: Yes

Light characteristics

- Beam angle: - degree(s)
- Color consistency: 6 SDCM
- Color rendering index (CRI): 90
- Warm-up time to 60% light: <2

Miscellaneous

- Especially designed for: Home office & Study
- Style: Functional
- Type: Desk/table

Other characteristics

- Lamp current: 900 mA
- Efficacy: 17 lm/W

Product dimensions & weight

- Height: 39 cm
- Length: 15.5 cm
- Net weight: 0.37 kg
- Width: 9.4 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Total lumen output fixture: 80
- Light color: 3000-4000-5700
- Mains power: 5 V
- Fixture dimmable: Yes
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 4.5
- IP code: IP20
- Class of protection: Class III



Issue date: 2023-11-08
Version: 0.64

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com