

# PHILIPS

Bulb

LED

8W-60W

B22

3000/4000/6500

8719514478992



## Selectable colour temperatures help you to make the right choice

Philips LED light bulbs provide a beautiful light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

### High quality light

- Designed for the comfort of your eyes

### Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years

### Light beyond illumination

- Instant on

# Highlights

## Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get

the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## Instant on

## 15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: B22
- Type of glass: Frosted
- Bulb Finish: Frosted
- Bulb Material: Plastic

## Bulb dimensions

- Height: 11.6 cm
- Width: 6 cm

## Design and finishing

- Material: Plastic

## Durability

- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000
- Ambient temperature range: -20 °C to 45 °C

## Light characteristics

- Beam angle: 200 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 3000/4000/6500 K
- Nominal luminous flux: 806 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 3000/4000/6500
- Correlated Color Temperature (Nom): 3000, 4000, 6500 K
- Luminous Efficacy (rated) (Nom): 100 lm/W
- Luminous Flux: 806 lm

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Efficacy: 100 lm/W
- EU RoHS compliant: Yes

**Packaging information**

- EAN: 8719514478992
- EOC: 871951447899200
- Product title: LEDBulb 8W B22 DS FR ND 1CT/6 AU

**Power**

- Power Factor (Fraction): 0.4

**Power consumption**

- Power factor: 0.4
- Voltage: 220–240 V
- Wattage: 8 W
- Wattage equivalent: 60 W
- Power Consumption: 8 W

**Product dimensions and weight**

- Length: 11.6 cm

**Rated values**

- Rated lifetime: 15,000 hour(s)

**Technical specifications**

- Frequency: 50–60 Hz
- Dimmable: No
- Line Frequency: 50 to 60 Hz
- Cap-Base: B22

**Packaging dimensions and weight**

- EAN/UPC – product: 8719514478992
- Net weight: 0.05 kg
- Gross weight: 0.06 kg
- Height: 14.9 cm
- Length: 6.3 cm
- Width: 6.3 cm
- Material number (12NC): 929003572219



Issue date: 2024-02-05  
Version: 0.56

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)