

PHILIPS

Ceiling light

Functional

CL610

White

RF Dimming



8719514483675



Set your desired ambiance at your fingertips

Create the right ambience every time. With just a couple of clicks on the remote control, Philips LED all-in-one ceiling light gives you the flexibility and convenience to choose between a range of light settings for every moment.

Premium quality

- EyeComfort - light that's easy on the eyes

Control

- Dimmable
- Remote control provides easy control of light settings up to 10M



Highlights

Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philip

s LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Dimmable

Allows you to change the mood by reducing LED brightness levels, from bright white light, to a cozy glow – just like traditional lamps.

Remote control provides easy control of light settings up to 10M

Turn lights on or off or change brightness and color from up to 10m away with this remote control.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Round

Design and finishing

- Color: White
- Material: Metal, Plastic

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 15,000

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: Yes
- LED integrated: Yes
- Remote control included: Yes

Light characteristics

- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Warm-up time to 60% light: <2

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office, Garage
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes

Other characteristics

- Lamp current: 186 mA
- Efficacy: 105 lm/W

Power consumption

- Power factor: 0.9

Product dimensions and weight

- Net weight: 1.03 kg
- Height: 8.1 cm
- Length: 48.5 cm
- Width: 48.5 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 485 mm
- Total lumen output fixture: 3800
- Light color: 2700/4000/6500
- Mains power: AC 220–240
- Fixture dimmable: RF Dim – Do not use with dimmer
- LED: Yes
- Wattage bulb included: 36
- IP code: IP20
- Class of protection: Class I

Packaging dimensions and weight

- EAN/UPC – product: 8719514483675
- Net weight: 1.03 kg
- Gross weight: 1.88 kg
- Height: 55 cm
- Length: 9.5 cm
- Width: 54.5 cm
- Material number (12NC): 929003263307



Issue date: 2024-02-02
Version: 0.85

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com