

PHILIPS

Neon flex strip 3m
kit

Smart LED

Full color

Low Voltage

IP20/Silicon



8720169187153



Create your light shape

Light can shape your mood, and now you can shape your light, with bendable Neon Flex Strips from Philips. With 3 meters of flexible light strip to play work, we're sure you can create clever and delightful shapes to beautify any room. Set the mood with neon gradient color effects. And because they have WiZ connected technology on board, you can easily control them using your Wi-Fi and the WiZ app, remote, or your voice.

Easy setup

- Easy plug and play

Smart control

- Control from anywhere with your smartphone
- Go hands-free with voice control

Smart features

- Automate your light with schedules

Light modes

- Millions of colors and dynamic light modes
- Multicolor with gradient effect

Form factor

- Create unique shapes with bendable light strips

Highlights

Easy plug and play



WiZ works with your existing Wi-Fi router, no additional gateway is needed. Simply plug in your new light, download the WiZ app and you're ready to go!

Control from anywhere




Control your WiZ lights wherever you are with smartphone. No need to worry if you've left your lights on before leaving home. WiZ app is available for iOS and Android.

Go hands-free with voice control



Control your lights with just the sound of your voice, simply enable integration with Google, Alexa or add to your Siri shortcuts.

Automate your light with schedules



Automate the lights to fit your daily or weekly routines. Schedule your light to turn on before you arrive home and keep it off when not needed.

Millions of colors and dynamic light modes



Choose from a palette of millions of light colors to create an amazing atmosphere in your home. Enjoy the subtle differences that our dynamic light effects glow your environment.

Gradient colors



This 3m light strip is designed with gradient effect. Set dynamic light modes with the WiZ app to create a pleasing, dynamic ambience.

Easy to shape



Bend these light strips into a circle, a star, a heart, a musical note, etc. Light strips mount easily with the included wall-mounting accessories.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Color: White
- Material: Plastic

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 50,000

Extra feature/accessory incl.

- Dimmable with remote control: Yes
- LED integrated: Yes
- On/off switch on wire: Yes
- Power adapter included: Yes
- Remote control included: No

Light characteristics

- Color rendering index (CRI): N.A.
- Warm-up time to 60% light: <2

Lightstrip

- Output Power: 20

Miscellaneous

- Especially designed for: Ambience

Other characteristics

- Lamp current: 125 mA

Power consumption

- Power factor: 0.7
- Voltage: 220-240 V

Product dimensions and weight

- Net weight: 0.6 kg
- Height: 1.7 cm
- Length: 300 cm
- Width: 1 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Total lumen output fixture: /
- Light color: RGB
- Fixture dimmable: Wireless Dim - Do not use with dimmer
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 24
- IP code: IP20
- Class of protection: Class II

Packaging dimensions and weight

- EAN/UPC - product: 8720169187153
- Net weight: 0.6 kg
- Gross weight: 0.9 kg
- Height: 8.7 cm
- Length: 22.4 cm
- Width: 22.4 cm
- Material number (12NC): 929003296107



Issue date: 2024-02-02
Version: 0.87

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com