

PHILIPS



Lois

9290046414

9290046415

9290046416

9290046417

9290046418

9290046419

9290046420

9290046421




User manual
Benutzerhandbuch
Notice d'emploi
Manual de usuario
Manual do usuário
Manuale d'uso
Gebruiksaanwijzing

Incl.




1x




	 (m ²)	
10W	0.0063 m ²	0.3m
20W	0.0104 m ²	0.3m
30W	0.0168 m ²	0.5m
50W	0.0245 m ²	0.5m





Excl.



2x  Ø6x30mm
2x  ST4.2x29mm




	
10W	3mm
20W	3mm
30W	4mm
50W	5mm








10NC	W	VAC	Hz	Im	K	PF
9290046414	10	220-240V	50/60	950	3000	>0.9
9290046415	10			950	5000	
9290046416	20			2050	3000	
9290046417	20			2050	5000	
9290046418	30			3200	3000	
9290046419	30			3200	5000	
9290046420	50			5400	3000	
9290046421	50			5400	5000	

mm





	L	H	W	
10W 830/850 BK	105	87	24	0.146kg
20W 830/850 BK	130	112	24	0.215kg
30W 830/850 BK	158	145	28	0.355kg
50W 830/850 BK	196	165	28	0.508kg







5



6





Signify Commercial UK Limited
Unit 3, Guildford Business Park,
Guildford, Surrey, GU2 8XG, UK

Signify
I.B.R.S. / C.C.R.I. Numéro 10461
5600 VB Eindhoven, the Netherlands
00800-74454775

Philips and the Philips Shield Emblem
are registered trademarks of Koninklijke
Philips N.V. and are used under license.

www.philips.com/lighting

© 2024 Signify Holding
Signify

3241 662 14352