



**A**

User manual  
Benutzerhandbuch  
Notice d'emploi  
Manual de usuário  
Manual do usuário  
Manuale d'uso

  
**hue**

Signify  
I.B.R.S. / C.C.R.I. Numéro 10461  
5600 VB Eindhoven,  
the Netherlands  
00800-74454775  
© 2025 Signify Holding  
All rights reserved  
Last update: 03/2025

www.philips-hue.com  
442296691711




Incl.

**A** 7 m  
**B** 14 m  
21 m

EU CH  
UK ANZ

Excl.



2

**B**

TYPE Z

! 0-14


EU IP44  
CH IP55  
UK IP20  
ANZ IP20

Model ID: A

IP65 III LED


3

1



2

A



B

4


!



www.philips-hue.com


5

!




6

!




7

3a




30 cm

3b




30 cm

!




≤ 7 m

!




≤ 03.5 mm

!




4




1 2

!




1 2

!




> 30 cm

5




EU CH




UK ANZ

!



!

Compatible with outdoor Hue Low-volt system



230V 40W 24V 8W 9W 17W 26W


Sample set up, add up the wattage of the lights:

8W + 8W + 9W 17W 26W ≤ 40W

12

!

Use maximum of 10 m extension cable for Festavia




max. 10 m 30W 24V 230V

Sample set up, add up the wattage of the lights:

9W 17W 26W ≤ 30W


13

!




X

!




!




Model ID: A

3



4



1 2

5

