



A

User manual  
Benutzerhandbuch  
Notice d'emploi  
Manual de usuário  
Manual do usuário  
Manuale d'uso

Incl. **A** **B**

**hue**

Signify  
I.B.R.S. / C.C.R.I. Numéro 10461  
5600 VB Eindhoven,  
the Netherlands  
00800-74454775  
© 2025 Signify Holding  
All rights reserved  
Last update: 09/2025

www.philips-hue.com  
442280011392

Incl. **A** **B**

EU CH  
UK ANZ

Excl.

2

**B**

TYPE Z

0-14

EU IP44  
CH IP55  
UK IP20  
ANZ IP20

IP67

LED

**G**

3

MAX. 20m  
MAX. 20m  
MAX. 20m  
MAX. 10m

4

1

hue  
Hue app

2

A

B

5

www.philips-hue.com

6

7

3a

A

B

25-30 cm 25-30 cm

8

C

D

click

9

3b

A

9

B

C

click

10

4

5a

>30 cm

5b

>30 cm

11

1

2

6

1

2

12

7

EU CH  
UK ANZ

H<sub>2</sub>O

13

Compatible with outdoor Hue Low-volt system

230V 40W 24V 8W 30W

Sample set up, add up the wattage of the lights:  
8W + 30W ≤ 40W

14