



3 3/4" (95mm) aperture  
Line Voltage 120V ES/ESD16  
Remodeler (Non-IC)

Lytecaster  
Recessed Downlight

**300ESX**



Complete fixture consists of Reflector Trim & Power Pack. Select each separately

POWER PACK	CUT-OUT	REFLECTOR TRIM
<b>300ESX</b>	3 3/4" (95mm)	Accepts most 3 3/4" (95mm) 300 serie trims ; see Reflector Trim specification sheets.

#### Features

**Power Pack** : Ideal for remodeling. Integral junction box with snap-off covers permits wiring from below.

**Socket** : Porcelain body ; Twist and lock (GZ base) Pre-wired with 18 ga. Teflon 250° leads to junction box.

**Thermal Protector** : Meets CSA/UL requirements. Insulation, if used, must be kept 3" (76mm) away from luminaire sides and junction box.

**Branch Wiring** : Certified for branch circuit wiring ; 4 x 14ga min.90° C supply conductors.

#### Accessories

**Thermal Protector Replacement** : 1970

**Labels** : CSA , UL

Damp or Wet location rated depending on trim used.