


Residential Anchor Base Post (394) Specification Sheet

| | | |
|---------------|--------------|------------|
| Project Name: | Location: | MFG: Hadco |
| Fixture Type: | Catalog No.: | Qty: |



Ordering Guide

Example: 394 6 ABS B B D

| | | |
|-----------------------------------|--|--|
| Product Code | 394 | Residential Anchor Base Post |
| Height(s) | 6 7 8 9 10 | (6 ft.) (7 ft.) (8 ft.) (9 ft.) (10 ft.) |
| Finish | ABS ACP ARD ASI BLK BRN BRZ FGN GRA IRN RBZ SRT VBZ VCP VGN VTC WBZ WHT | Antique Brass Antique Copper Antique Red Antique Silver Black Brown Bronze Forest Green Granite Ironstone Rustic Bronze Shadow Rust Verde Bronze Verde Copper Verde Vintage Copper Weathered Bronze White |
| Photoeye (Optional) | B C D | 120V 208V - 277V 120V only (for 3" OD Post) |
| Outlet Location (Optional) | B T | 4" from Top of Base 12" from Top of Pole |
| Outlet Options (Optional) | D G | Standard Duplex GFI Duplex |

Specifications

OUTLET:

GFI Duplex Outlet has dual-function indicator light, universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant. Standard Duplex Outlet has universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant.

CONSTRUCTION:

Cast aluminum anchor base. Cast aluminum removable access door. Straight post welded to base.

FINISH:

Resilient TGIC thermoset polyester powdercoat paint is electrostatically applied to every fixture. Specially formulated for Hadco Outdoor Lighting, it provides UV protection, and the highest temperature rating in the industry. In addition to the standard color choices shown, a spectrum of custom colors is available.

WARRANTY:

Lifetime limited warranty.

Residential Anchor Base Post (394) Specification Sheet

Project Name:

Location:

MFG: Hadco

Fixture Type:

Catalog No.:

Qty:

Tenon/Top:

3" O.D.

Anchor Rods:

(1) 3/4" dia. x 18" long galvanized steel

Base Dimensions:

8 5/8" dia. x 18 1/2"

Shaft:

3" Straight

Wall Thickness:

.125"

Height:

6', 7', 8', 9', 10'

