


# PHILIPS

Abelia



User manual  
Benutzerhandbuch  
Notice d'emploi  
Manual de usuario  
Manual do usuário  
Manuale d'uso  
Gebruiksaanwijzing

Incl.







Excl.




IPX4








MAX




Min. = 10 Lumen

⌚ >100h





ON = 220 Lumen



⌚ 4h




Max. = 350 Lumen

⌚ 2h30







%0



%100





Signify  
I.B.R.S. / C.C.R.I. Numéro 10461  
5600 VB Eindhoven,  
the Netherlands  
☎00800-74454775

© 2021 Signify Holding  
All rights reserved

[www.philips.com/lighting](http://www.philips.com/lighting)

17360/\*\*/PO  
4404 029 06613  
Last update: 06/2021