



Essential SmartBright All-in-one Solar Pathway

BRC010 LED40/MCCT G2

Integrated solar pathway light with Lithium Ferro Phosphate battery, solar panel and charger built into the luminaire. Optional wall mounting arm bracket. Microwave based motion sensor for optimizing battery autonomy.

Warnings and Safety

- Not recommended to install this luminaire higher than 4 meters height.
- Install the luminaire in a sunny place that is not shaded by trees, buildings and walls, then the solar panel can receive the maximum sunlight for charging the battery.
- Charge the product under sunlight for at least 8 hours before first time using.
- It works 100% on solar energy. This luminaire does not need any external electrical connection.

Product data

General Information	
Driver included	Yes
Value ladder	Value
Warranty period	1 years
Light Technical	
Luminous Flux	4,000 lm
Correlated Color Temperature (Nom)	2200 6500 K
Luminous Efficacy (rated) (Nom)	160 lm/W
Color rendering index (CRI)	70

Operating and Electrical	
Battery type	LiFePO4
Battery ampere hour	15 Ah
Battery voltage	3.2 V
Battery charging & discharging cycles	500
Panel type	Mono crystalline
Panel voltage	4.5 V
Panel peak wattage	14 W
Charge controller type	PWM
Connection	-
Cable	-

Essential SmartBright All-in-one Solar Pathway

Grid connection type	Off grid
Controls and Dimming	
Dimmable	Preset Dimming
Configurability	Not configurable
Control interface	-
Solar dimming profile	Preset Dimming
Mechanical and Housing	
Housing Color	Grey
Overall length	508 mm
Overall width	228 mm
Overall height	44.5 mm
Dimensions (Height x Width x Depth)	45 x 228 x 508 mm
Material	Polycarbonate
Battery location	Inbuilt luminaire
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Optical cover type	Polycarbonate
Net Weight (Piece)	2.130 kg

Approval and Application	
CE mark	Yes
EU RoHS compliant	Yes
Ambient temperature range	0 °C to 45 °C
Product Data	
Order product name	BRC010 LED40/MCCT G2
Full product name	BRC010 LED40/MCCT G2
Full product code	872110332994399
Order code	911401809803
Material Nr. (12NC)	911401809803
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103329943
Numerator - Packs per outer box	5
EAN/UPC - Case	8721103329967

Dimensional drawing

