



Essential SmartBright LED Solar Flood

BVC010 LED20/765 Solar

Solar flood light with lithium ferro phosphate battery built in the luminaire, Remote controller and installation accessories included. IP65, plastic housing. Available in 600, 1000, 2000, 3000, 4000, 5000 and 6000 Lumens

Warnings and Safety

- Install the luminaire in a sunny place that is not shaded by trees, buildings and walls, then the solar panel can receive the maximum sunlight for charging the battery.
- Charge the product under sunlight for at least 8 hours before first time using.
- This luminaire does not need any external electrical connection. It works 100% on solar energy.

Product data

General Information	
Driver included	Yes
Warranty period	1 years
Light Technical	
Luminous Flux	2,000 lm
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	165 lm/W
Color rendering index (CRI)	70
Operating and Electrical	
Line Frequency	- Hz
Battery type	LiFePO4
Battery ampere hour	5 Ah
Battery voltage	3.2 V
Battery charging & discharging cycles	500

Panel type	Mono crystalline
Panel voltage	5 V
Panel peak wattage	8 W
Charge controller type	PWM
Cable connection kit	Included
Connection	-
Cable	-
Grid connection type	Off grid
Controls and Dimming	
Dimmable	Preset Dimming
Configurability	Not configurable
Control interface	-
Solar dimming profile	Preset Dimming

Essential SmartBright LED Solar Flood

Mechanical and Housing	
Housing Color	Grey
Overall length	160 mm
Overall width	215 mm
Overall height	53 mm
Dimensions (Height x Width x Depth)	53 x 215 x 160 mm
Material	Acrylonitrile-butadiene-styrene
Battery location	Inbuilt luminaire
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Optical cover type	Polycarbonate
Net Weight (Piece)	1.450 kg

Approval and Application

CE mark	Yes
EU RoHS compliant	Yes

Ambient temperature range	0 to +45 °C
Product Data	
Order product name	BVC010 LED20/765 Solar
Full product name	BVC010 LED20/765 Solar
Full product code	872110333707899
Order code	911401812603
Material Nr. (12NC)	911401812603
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103337078
Numerator - Packs per outer box	5
EAN/UPC - Case	8721103337528

Dimensional drawing

