



Solar Panel Sub System

Hex Vertical PV panel 100Wp 43V BC

A Range of Solar panels from 20 W to 325 W specially designed for Philips Solar Street lighting, Flood lighting and Solar Indoor Systems

Product data

General Information	
Value ladder	Value
Operating and Electrical	
Panel type	Mono crystalline
Panel voltage	43 V
Panel peak wattage	100 W
Mechanical and Housing	
Overall length	824 mm
Overall width	256 mm
Overall height	256 mm
Dimensions (Height x Width x Depth)	256 x 256 x 824 mm
Net Weight (Piece)	9.650 kg
Approval and Application	
CE mark	Yes

EU RoHS compliant	Yes
Ambient temperature range	-40 °C to 85 °C
Product Data	
Order product name	Hex Vertical PV panel 100Wp 43V BC
Full product name	Hex Vertical PV panel 100Wp 43V BC
Full product code	872110333918800
Order code	911401816903
Material Nr. (12NC)	911401816903
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103339188
Numerator - Packs per outer box	1
EAN/UPC - Case	8721103339188

Solar Panel Sub System

Dimensional drawing

