




Solar Panel Sub System

Sqr Vertical PV panel 100Wp 43V BC

A Range of Solar panels from 20 W to 325 W specially designed for Philips Solar Street lighting, Flood lighting and Solar Indoor Systems

Product data

General Information	
Value ladder	Value
Operating and Electrical	
Panel type	Mono crystalline
Panel voltage	43 V
Panel peak wattage	100 W
Mechanical and Housing	
Overall length	832 mm
Overall width	225 mm
Overall height	225 mm
Dimensions (Height x Width x Depth)	225 x 225 x 832 mm
Net Weight (Piece)	9.850 kg
Approval and Application	
CE mark	Yes

EU RoHS compliant	Yes
Ambient temperature range	-40 °C to 85 °C
Product Data	
Order product name	Sqr Vertical PV panel 100Wp 43V BC
Full product name	Sqr Vertical PV panel 100Wp 43V BC
Full product code	872110370195400
Order code	911401831803
Material Nr. (12NC)	911401831803
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103701954
Numerator - Packs per outer box	1
EAN/UPC - Case	8721103701954

Solar Panel Sub System

Dimensional drawing

