




Solar Panel Sub System

Sqr Vertical PV panel 300Wp 43V BC

A Range of Solar panels from 20 W to 325 W specially designed for Philips Solar Street lighting, Flood lighting and Solar Indoor Systems

Product data

General Information	
Value ladder	Value
Operating and Electrical	
Panel type	Mono crystalline
Panel voltage	43 V
Panel peak wattage	300 W
Mechanical and Housing	
Overall length	1,958 mm
Overall width	225 mm
Overall height	225 mm
Dimensions (Height x Width x Depth)	225 x 225 x 1958 mm
Net Weight (Piece)	18.900 kg
Approval and Application	
CE mark	Yes

EU RoHS compliant	Yes
Ambient temperature range	-40 °C to 85 °C
Product Data	
Order product name	Sqr Vertical PV panel 300Wp 43V BC
Full product name	Sqr Vertical PV panel 300Wp 43V BC
Full product code	872110370197800
Order code	911401832003
Material Nr. (12NC)	911401832003
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103701978
Numerator - Packs per outer box	1
EAN/UPC - Case	8721103701978

Solar Panel Sub System

Dimensional drawing

