



Essential SmartBright Solar Post Top

BPC010 LED30/MCT Solar post top Pro

A range of solar all in one post top with unique feature of selectable color temperature

Warnings and Safety

- Install the product in a place with adequate sunlight without shades of trees, building, walls etc. for faster charging of battery

Product data

General Information	
Driver included	Yes
Value ladder	Value
Warranty period	2 years
Light Technical	
Luminous Flux	3,000 lm
Correlated Color Temperature (Nom)	3000 4000 6500 K
Luminous Efficacy (rated) (Nom)	165 lm/W
Color rendering index (CRI)	70
Operating and Electrical	
Battery type	Lithium Ferro Phosphate
Battery ampere hour	14.4 Ah
Battery voltage	3.2 V
Panel type	Poly crystalline
Panel voltage	4.5 V
Panel peak wattage	13 W
Grid connection type	Off grid

Controls and Dimming	
Dimmable	Yes
Configurability	Not configurable
Solar dimming profile	Pre-configured
Mechanical and Housing	
Housing Color	Gray
Overall length	420 mm
Overall width	420 mm
Overall height	123 mm
Overall diameter	420 mm
Dimensions (Height x Width x Depth)	123 x 420 x 420 mm
Material	Polycarbonate
Battery location	In built
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Optical cover type	Polycarbonate
Net Weight (Piece)	3.040 kg

Essential SmartBright Solar Post Top

Approval and Application	
Ambient temperature range	0 °C to 55 °C
Over Time Performance (IEC Compliant)	
Median useful life L70B50	25,000 hour(s)
Product Data	
Order product name	BPC010 LED30/MCT Solar post top Pro
Full product name	BPC010 LED30/MCT Solar post top Pro

Full product code	692382861017399
Order code	911401876502
Material Nr. (12NC)	911401876502
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828610173
Numerator - Packs per outer box	2
EAN/UPC - Case	6923828610227

