



# Exit Sign

## EM159C WL/CM EXIT SIGN M3 ELP UP WH

Exit Sign, Illuminated emergency exit sign, 3 W, 3 W, 313x212mm; H42 mm, 23 lm, 6500 K, IP20, ELP3h

Illuminated emergency exit sign, 313x212mm; H42 mm, Polycarbonate, White, Signal white (RAL9003), 23 lm, 3 W, 22 lm/W, 6500 K, 0.33, Clear, UV-stabilised polycarbonate cover, IP20 | Finger-protected, IK03 | 0.3 J, Safety class II, 2 push-in connectors 3-pole, Emergency lighting 3-hour duration Pro version

### Product data

General Information		Effective projected area	
Lamp family code	-	Effective projected area	1 m <sup>2</sup>
Number of gear units	Unit	Operating and Electrical	
Driver included	Yes	Input Voltage	220-240 V
Light source engine type	LED	Line Frequency	50 Hz
Service Tag	No	Initial CLO power consumption	3 W
Warranty period	5 years	Average CLO power consumption	3 W
		End CLO power consumption	3 W
Light Technical		Inrush current	4.39 A
Upwards light output ratio	34.8	Inrush time	100 ms
Luminous Flux	23 lm	Power Consumption	3 W
Correlated Colour Temperature (Nom)	6500 K	Power Factor (Fraction)	0.35
Luminous efficacy (rated) (nom.)	22 lm/W	Connection	2 push-in connectors 3-pole
Colour rendering index (CRI)	>80	Cable	-
Light source colour	6500	Number of products on MCB (16 A type B)	228
Optic type	-	Suitable for random switching	Not applicable
Luminaire light beam spread	235°	Protection class IEC	Safety class II
Optic type outdoor	-		

# Exit Sign

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	-
Control interface	Internal (no external connection)
Constant light output	No
Maximum dim level	Not applicable
Embedded control	-

Mechanical and Housing	
Housing material	Polycarbonate
Reflector material	-
Optic material	Polycarbonate
Optical cover/lens material	UV-stabilised polycarbonate cover
Fixation material	-
Housing Colour	White
Mounting device	-
Optical cover/lens finish	Clear
Reflector finish	-
Overall length	313 mm
Overall width	212 mm
Overall height	42 mm
Dimensions (height x width x depth)	42 x 212 x 313 mm
Parts colour	All parts coloured
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Standard tilt angle post-top	0°
Standard tilt angle side entry	0°
Optical cover type	-
Net Weight (Piece)	0.520 kg

Emergency Operation	
Emergency flux	23 lm
Rated duration of the emergency lighting (when fully charged)	3 h
Additional max. power consumption when emergency battery is charging	3 W
Central Emergency	No
Emergency lighting	Emergency lighting 3-hour duration Pro version
Emergency function testing method	Automatic pre-programmed self testing
Emergency lighting operation mode	Maintained

Approval and Application	
Glow-wire test	-
Flammability mark	-
CE mark	Yes
ENEC mark	-
Photobiological risk	Photobiological risk group 0 @ 200mm to EN62471

Photobiological risk specification	0 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	+5 to +45 °C

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-5%
Initial chromaticity	0.33
Power consumption tolerance	+/-10%
Init. Colour Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 35,000 h	5 %
Control gear failure rate at median useful life 50,000 h	10 %
Control gear failure rate at median useful life 50,000 h	25 %
Control gear failure rate at median useful life 100,000 h	50 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 35000 h	L95
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L95
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 75000 h	L90
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L90

Sustainability Data	
Sustainability rating	Unclassified
Repair class	Repair Class D, this product is not designed to be repaired.

Product Data	
Order product name	EM159C WL/CM EXIT SIGN M3 ELP UP WH
Full product name	EM159C WL/CM EXIT SIGN M3 ELP UP WH
Full EOC	871869979904500
Order code	912401483519
Material no. (12 NC)	912401483519
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718699799045
Numerator – packs per outer box	10
EAN/UPC - Case	8719514880016

# Exit Sign

## Dimensional drawing

