



HID ignitors for series systems

SI 51 220-240V 50/60Hz

HID ignitors for series systems


Product data

| Operating and Electrical | |
|--------------------------|-----------------------------|
| Input Voltage | 220 to 240 V |
| Line Frequency | 50 to 60 Hz |
| Input frequency | 50 to 60 Hz |
| Wiring | |
| Connector type | Screw |
| Temperature | |
| T-Case maximum (max.) | 80 °C |
| Mechanical and Housing | |
| Housing | SNI-85 |
| Net Weight (Piece) | 0.040 kg |
| Approval and Application | |
| Approval marks | CE marking ENEC certificate |

| CE mark | No |
|---------------------------------|------------------------|
| Ambient temperature range | -20°C to 75°C |
| Product Data | |
| Order product name | SI 51 220-240V 50/60Hz |
| Full product name | SI 51 220-240V 50/60Hz |
| Full EOC | 871150091553530 |
| Order code | 913619519966 |
| Material no. (12 NC) | 913619519966 |
| Local order code | SI51 |
| Numerator – quantity per pack | 1 |
| EAN/UPC – Product/Case | 8711500915535 |
| Numerator – packs per outer box | 48 |
| EAN/UPC - Case | 8711500908353 |

HID ignitors for series systems

Dimensional drawing



| Product | D1 | C1 | A1 | A2 | B1 |
|------------------------|--------|---------|---------|---------|---------|
| SI 51 220-240V 50/60Hz | 4.3 mm | 38.0 mm | 84.5 mm | 65.0 mm | 41.0 mm |

