



# HID ignitors for series systems

## SND 58 220-240V 50/60Hz

HID ignitors for series systems


### Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Wiring	
Connector type	Screw
Temperature	
T-Case maximum (max.)	90 °C
Mechanical and Housing	
Housing	SNI-85
Net Weight (Piece)	0.050 kg
Approval and Application	
Approval marks	CE marking ENEC certificate

CE mark	No
Ambient temperature range	-20°C to 85°C
Product Data	
Order product name	SND 58 220-240V 50/60Hz
Full product name	SND 58 220-240V 50/60Hz
Full EOC	871150093068230
Order code	913700185166
Material no. (12 NC)	913700185166
Local order code	SND58
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500930682
Numerator – packs per outer box	48
EAN/UPC - Case	8711500930699

## HID ignitors for series systems

### Dimensional drawing



Product	D1	C1	A1	A2	B1
SND 58 220-240V 50/60Hz	4.3 mm	38.5 mm	84.5 mm	65.0 mm	41.5 mm

