



HID-HighPower for SON/MH/HPL/HPI

BSN 1000 L78-A2 230/240V 50Hz HP-257

Encapsulated ballasts for use with SON (T) (Plus), HPL, HPI and MH lamps with rated wattages of 1000 W and above


Product data

Operating and Electrical	
Input Voltage	230 V (default) or 240 V
Line Frequency	50 Hz
Input frequency	50 Hz
Wiring	
Connector type	Screw
Mechanical and Housing	
Net Weight (Piece)	12.700 kg
Approval and Application	
Approval marks	CE marking ENEC certificate
CE mark	Yes

Product Data	
Order product name	BSN 1000 L78-A2 230/240V 50Hz HP-257
Full product name	BSN 1000 L78-A2 230/240V 50Hz HP-257
Full EOC	871150006236900
Order code	913700217503
Material no. (12 NC)	913700217503
Local order code	BSN1000L78
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500996640
Numerator – packs per outer box	1
EAN/UPC - Case	8711500062369

HID-HighPower for SON/MH/HPL/HPI

Dimensional drawing



Product	D1	C1	A1	A2	A3	B1	B2
BSN 1000 L78-A2	6.5	102.0	257.0	222.0	246.0	117.0	88.0
230/240V 50Hz	mm	mm	mm	mm	mm	mm	mm
HP-257							

