

HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

BSN 70 L33-A2-TS 230V 50Hz HD1-118

Encapsulated electromagnetic copper/iron ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps

Product data

Operating and Electrical	
Input Voltage	230 V
Line Frequency	50 Hz
Input frequency	50 Hz

Wiring	
Connector type	Screw


Mechanical and Housing	
Net Weight (Piece)	1.280 kg

Approval and Application	
Approval marks	CE marking ENEC certificate

Product Data	
Order product name	BSN 70 L33-A2-TS 230V 50Hz HD1-118
Full product name	BSN 70 L33-A2-TS 230V 50Hz HD1-118
Full EOC	871150005968031
Order code	913700226526
Material no. (12 NC)	913700226526
Local order code	BSN70L33TS
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500059680
Numerator – packs per outer box	6
EAN/UPC - Case	8711500062154

HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 70 L33-A2-TS 230V 50Hz	6.2 mm	53.0 mm	118.0 mm	103.0 mm	65.0 mm
HD1-118					

