



HID-Basic BHL MK4 for HPL/HPI

BHL 250 K307-A2 230/240V 50Hz BC2-134

Impregnated electromagnetic copper/iron ballasts for HPL, HPI (Plus) and SON-H lamps

Product data

Operating and Electrical	
Input Voltage	230 V (default) or 240 V
Line Frequency	50 Hz
Input frequency	50 Hz

Wiring	
Connector type	Screw


Mechanical and Housing	
Net Weight (Piece)	2.245 kg

Approval and Application	
Approval marks	CE marking ENEC certificate

Product Data	
Order product name	BHL 250 K307-A2 230/240V 50Hz BC2-134
Full product name	BHL 250 K307-A2 230/240V 50Hz BC2-134
Full EOC	872790088701300
Order code	913700278026
Material no. (12 NC)	913700278026
Local order code	BHL250K307
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500881588
Numerator – packs per outer box	6
EAN/UPC - Case	8727900887013

HID-Basic BHL MK4 for HPL/HPI

Dimensional drawing



Product	D1	C1	A1	A2	B1
BHL 250 K307-A2 230/240V 50Hz	6.2 mm	65.0 mm	134.0 mm	113.0 mm	76.0 mm
BC2-134					

