



# HF-Performer II for PL-T/C/R/L/TL5C lamps

## HF-P 2 22-42 PL-T/C/L/TL5C EII 220-240V

HF-Performer EII PL-T/C/R/T5c is a sustainable, slim and high-frequency electronic ballast for a wide range of CFL- ni applications. It is ideal for applications where high energy efficiency is required. The HF-Performer EII range has a robust design, meets all relevant international safety and performance standards and is energy-efficient (CELMA EEI A2).

### Product data

| Operating and Electrical                       |              |
|------------------------------------------------|--------------|
| Input Voltage                                  | 220 to 240 V |
| Line Frequency                                 | 50 to 60 Hz  |
| Input frequency                                | 50 to 60 Hz  |
| Inrush current width                           | 0.35 ms      |
| Inrush current peak (max.)                     | 31 A         |
| Number of products on MCB (16 A type B) (nom.) | 12           |
| Wiring                                         |              |
| Connector type input terminals                 | Insert       |
| Connector type output terminals                | Insert       |
| Temperature                                    |              |
| T-case lifetime (nom.)                         | 75 °C        |
| T-Case maximum (max.)                          | 75 °C        |


| Mechanical and Housing    |                                                 |
|---------------------------|-------------------------------------------------|
| Ingress protection code   | IP20 [Finger-protected]                         |
| Net Weight (Piece)        | 0.150 kg                                        |
| Approval and Application  |                                                 |
| Energy efficiency index   | A2                                              |
| Safety standard           | IEC 61347-2-3                                   |
| Environmental standard    | ISO 14001                                       |
| Approval marks            | CE marking ENEC certificate VDE-EMV certificate |
| CE mark                   | Yes                                             |
| Ambient temperature range | -25°C to 50°C                                   |
| Product Data              |                                                 |
| Order product name        | HF-P 2 22-42 PL-T/C/L/TL5C EII<br>220-240V      |

HF-Performer II for PL-T/C/R/L/TL5C lamps

|                      |                                            |
|----------------------|--------------------------------------------|
| Full product name    | HF-P 2 22-42 PL-T/C/L/TL5C EII<br>220-240V |
| Full EOC             | 871150091399930                            |
| Order code           | 913700630866                               |
| Material no. (12 NC) | 913700630866                               |
| Local order code     | HFP22242PLT/C/L                            |

|                                 |               |
|---------------------------------|---------------|
| Numerator – quantity per pack   | 1             |
| EAN/UPC – Product/Case          | 8711500913999 |
| Numerator – packs per outer box | 12            |
| EAN/UPC – Case                  | 8711500914019 |

Dimensional drawing



| Product                                     | D1     | C1      | A1       | A2      | B1      | B2      |
|---------------------------------------------|--------|---------|----------|---------|---------|---------|
| HF-P 2 22-42 PL-T/C/L/<br>TL5C EII 220-240V | 4.5 mm | 30.0 mm | 103.0 mm | 93.5 mm | 67.0 mm | 57.5 mm |

