

PrimaVision Mini for CDM

HID-PV m 35/I CDM 220-240V 50/60Hz


Miniature HID electronic gear for PGJ5 CDM lamps – freeing up the boundaries of creativity and innovation in luminaire design

Product data

| Operating and Electrical | | Approval and Application | |
|--|--------------|---------------------------------|--|
| Input Voltage | 220 to 240 V | Approval marks | F-Marking CE marking ENEC certificate CB certificate |
| Line Frequency | 50 to 60 Hz | CE mark | Yes |
| Input frequency | 50 to 60 Hz | Ambient temperature range | -20°C to 45°C |
| Earth leakage current (max.) | 0.5 mA | Product Data | |
| Inrush current width | 0.25 ms | Order product name | HID-PV m 35/I CDM 220-240V 50/60Hz |
| Inrush current peak (max.) | 15 A | Full product name | HID-PV m 35/I CDM 220-240V 50/60Hz |
| Number of products on MCB (16 A type B) (nom.) | 24 | Full EOC | 872790089164500 |
| Wiring | | Order code | 913700653566 |
| Cable length from device to lamp | 2 m | Material no. (12 NC) | 913700653566 |
| Connector type | Insert | Local order code | PVM35I |
| Temperature | | Numerator – quantity per pack | 1 |
| T-case lifetime (nom.) | 85 °C | EAN/UPC – Product/Case | 8711500881724 |
| T-Case maximum (max.) | 85 °C | Numerator – packs per outer box | 10 |
| Mechanical and Housing | | EAN/UPC - Case | 8727900891645 |
| Housing | Independent | | |
| Net Weight (Piece) | 0.230 kg | | |

PrimaVision Mini for CDM

Dimensional drawing



| Product | D1 | C1 | A1 | A2 | A3 | B1 |
|---------------------------------------|--------|---------|----------|----------|----------|---------|
| HID-PV m 35/I CDM 220-240V 50/60Hz | 4.8 mm | 34.0 mm | 234.7 mm | 225.1 mm | 202.0 mm | 49.4 mm |

