




HID ignitors for MK4 semi-parallel systems

SKD 578 220-240V 50/60Hz

HID ignitors for semi-parallel systems


Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Wiring	
Connector type	Screw
Temperature	
T-Case maximum (max.)	90 °C
Mechanical and Housing	
Net Weight (Piece)	30.000 g
Approval and Application	
Approval marks	CE marking ENEC certificate

CE mark	No
Ambient temperature range	-30°C to 85°C
Product Data	
Order product name	SKD 578 220-240V 50/60Hz
Full product name	SKD 578 220-240V 50/60Hz
Full EOC	872790089567400
Order code	913700655366
Material no. (12 NC)	913700655366
Local order code	SKD578
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8727900771312
Numerator – packs per outer box	48
EAN/UPC - Case	8727900895674

HID ignitors for MK4 semi-parallel systems

Dimensional drawing



Product	A1	B1	C1
SKD 578 220-240V 50/60Hz	63.5 mm	40.5 mm	28 mm

Product
SKD 578 220-240V 50/60Hz

