



# HF-Regulator Intelligent Touch DALI for TL5/TL-D/PL-L lamps

## HF-Ri TD 4 14/24 TL5 E+ 195-240V

This intelligent high-frequency electronic dimming ballast utilizes the DALI or Touch and Dim push-button protocol for fluorescent lamps. It meets A1BAT requirements, thereby pre-empting upcoming legislation. With a special command you can retrieve the system's mains power consumption, and with another you can find out which lamp wattage is connected. Combined with controls, additional energy savings can be achieved.

### Product data

Operating and Electrical	
Input Voltage	195-240 V
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Earth leakage current (max.)	0.5 mA
Inrush current width	0.26 ms
Inrush current peak (max.)	31 A
Number of products on MCB (16 A type B) (nom.)	16

Wiring	
Connector type input terminals	WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring]
Connector type output terminals	WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring]
Temperature	
T case lifetime (max.)	75 °C
T-Case maximum (max.)	75 °C

## HF-Regulator Intelligent Touch DALI for TL5/TL-D/PL-L lamps

Controls and Dimming	
Control interface	TD

Mechanical and Housing	
Housing	L 360x39x22
Ingress protection code	IP20 [Finger-protected]
Net Weight (Piece)	0.392 kg


Approval and Application	
Energy efficiency index	A1 BAT
Safety standard	IEC 61347-2-3
Environmental standard	ISO 14001
Approval marks	CE marking ENEC certificate VDE-EMV certificate
CE mark	Yes

Ambient temperature range	-25°C to 50°C
---------------------------	---------------

Product Data	
Order product name	HF-Ri TD 4 14/24 TL5 E+ 195-240V
Full product name	HF-Ri TD 4 14/24 TL5 E+ 195-240V
Full EOC	871829115678900
Order code	913700679166
Material no. (12 NC)	913700679166
Local order code	HFRITD41424T5E+
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718291156789
Numerator – packs per outer box	10
EAN/UPC – Case	8718291156796

### Dimensional drawing



Product	D1	C1	A1	A2	B1
HF-Ri TD 4 14/24 TL5 E+ 195-240V	4.2 mm	22.0 mm	360.0 mm	350.0 mm	39.0 mm

