



PrimaVision Mini for CDM

HID-PV m 20 /S CDM 220-240V 50/60Hz

Miniature HID electronic gear for PGJ5 CDM lamps – freeing up the boundaries of creativity and innovation in luminaire design


Product data

| Operating and Electrical | |
|--|--------------|
| Input Voltage | 220 to 240 V |
| Line Frequency | 50 to 60 Hz |
| Input frequency | 50 to 60 Hz |
| Earth leakage current (max.) | 0.5 mA |
| Inrush current width | 0.25 ms |
| Inrush current peak (max.) | 15 A |
| Number of products on MCB (16 A type B) (nom.) | 32 |
| Wiring | |
| Cable length from device to lamp | 0.5 m |
| Connector type | Insert |
| Temperature | |
| T-case lifetime (nom.) | 80 °C |
| T-Case maximum (max.) | 80 °C |
| Mechanical and Housing | |
| Housing | /S |

| Net Weight (Piece) | 0.115 kg |
|---------------------------------|---|
| Approval and Application | |
| Approval marks | CE marking ENEC certificate VDE certificate |
| Ambient temperature range | -20°C to 55°C |
| Product Data | |
| Order product name | HID-PV m 20 /S CDM 220-240V 50/60Hz |
| Full product name | HID-PV m 20 /S CDM 220-240V 50/60Hz |
| Full EOC | 871829167159600 |
| Order code | 913700696066 |
| Material no. (12 NC) | 913700696066 |
| Local order code | PVM20SHPF |
| Numerator – quantity per pack | 1 |
| EAN/UPC – Product/Case | 8718291671596 |
| Numerator – packs per outer box | 12 |
| EAN/UPC - Case | 8718291671602 |

PrimaVision Mini for CDM

Dimensional drawing



| Product | D1 | C1 | A1 | A2 | B1 |
|--|--------|---------|---------|---------|---------|
| HID-PV m 20 /S CDM 220-240V 50/60Hz | 4.2 mm | 30.2 mm | 97.3 mm | 88.3 mm | 43.3 mm |

