



HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/ HPI

BSN 50 K302-A2-ITS 230V 50Hz

Impregnated electromagnetic copper ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps



Product data

Operating and Electrical	
Input Voltage	230 V
Line Frequency	50 Hz
Input frequency	50 Hz
Wiring	
Connector type	Screw
Mechanical and Housing	
Net Weight (Piece)	1.260 kg
Approval and Application	
Approval marks	CE marking ENEC certificate
CE mark	Yes

Product Data	
Order product name	BSN 50 K302-A2-ITS 230V 50Hz
Full product name	BSN 50 K302-A2-ITS 230V 50Hz
Full EOC	871869674078100
Order code	913700751926
Material no. (12 NC)	913700751926
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696740781
Numerator – packs per outer box	6
EAN/UPC - Case	8718696740798

HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/HPI

Dimensional drawing



Product	A1	A2	B1	C1	D1
BSN 50 K302-A2-ITS 230V 50Hz	118 mm	94 mm	61 mm	52 mm	6.2 mm

