

HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

BSN 50 L33-A2-TS 230V 50Hz



Encapsulated electromagnetic copper/iron ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps

Product data

Operating and Electrical		Product Data	
Input Voltage	230 V	Order product name	BSN 50 L33-A2-TS 230V 50Hz
Line Frequency	50 Hz	Full product name	BSN 50 L33-A2-TS 230V 50Hz
Input frequency	50 Hz	Full EOC	871869674080400
		Order code	74080400
		Material no. (12 NC)	913700752026
		Numerator – quantity per pack	1
		EAN/UPC – Product/Case	8718696740804
		Numerator – packs per outer box	6
		EAN/UPC - Case	8718696740811
Wiring			
Connector type	Screw		
Mechanical and Housing			
Net Weight (Piece)	1.270 kg		
Approval and Application			
Approval marks	CE marking ENEC certificate		

HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

Dimensional drawing



Product	A1	A2	B1	C1	D1
BSN 50 L33-A2-TS 230V 50Hz	118 mm	103 mm	65 mm	53 mm	6.2 mm

