



HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

BSN 100 L33-A2-TS 230V 50Hz

Encapsulated electromagnetic copper/iron ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps

Product data

Operating and Electrical	
Input Voltage	230 V
Line Frequency	50 Hz
Input frequency	50 Hz
Wiring	
Connector type	Screw
Mechanical and Housing	
Net Weight (Piece)	1.380 kg
Approval and Application	
Approval marks	CE marking ENEC certificate

Product Data	
Order product name	BSN 100 L33-A2-TS 230V 50Hz
Full product name	BSN 100 L33-A2-TS 230V 50Hz
Full EOC	871869674094100
Order code	74094100
Material no. (12 NC)	913700752526
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696740941
Numerator – packs per outer box	6
EAN/UPC – Case	8718696740958

HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

Dimensional drawing



Product	A1	A2	B1	C1	D1
BSN 100 L33-A2-TS 230V 50Hz	123 mm	108 mm	65 mm	53 mm	6.2 mm

