



HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/ HPI

BSN 150 K302-A2-ITS 230V 50Hz

Impregnated electromagnetic copper ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps

Product data

Operating and Electrical	
Input Voltage	230 V
Line Frequency	50 Hz
Input frequency	50 Hz
Wiring	
Connector type	Screw
Mechanical and Housing	
Net Weight (Piece)	2.240 kg
Approval and Application	
Approval marks	CE marking ENEC certificate

Product Data	
Order product name	BSN 150 K302-A2-ITS 230V 50Hz
Full product name	BSN 150 K302-A2-ITS 230V 50Hz
Full EOC	871869674096500
Order code	74096500
Material no. (12 NC)	913700752626
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696740965
Numerator – packs per outer box	6
EAN/UPC - Case	8718696740972

HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/HPI

Dimensional drawing



Product	A1	A2	B1	C1	D1
BSN 150 K302-A2-ITS 230V 50Hz	134 mm	113 mm	76 mm	65 mm	6.2 mm

