

# HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

## BSN 150 L33-A2-TS 230V 50Hz

Encapsulated electromagnetic copper/iron ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps

### Product data

Operating and Electrical	
Input Voltage	230 V
Line Frequency	50 Hz
Input frequency	50 Hz

---

Wiring	
Connector type	Screw

---

Mechanical and Housing	
Net Weight (Piece)	1.910 kg



---

Approval and Application	
Approval marks	CE marking ENEC certificate
CE mark	Yes

Product Data	
Order product name	BSN 150 L33-A2-TS 230V 50Hz
Full product name	BSN 150 L33-A2-TS 230V 50Hz
Full EOC	871869674100900
Order code	913700752826
Material no. (12 NC)	913700752826
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696741009
Numerator – packs per outer box	6
EAN/UPC - Case	8718696741016

# HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

## Dimensional drawing



Product	A1	A2	B1	C1	D1
BSN 150 L33-A2-TS 230V 50Hz	126 mm	108 mm	81 mm	66 mm	6.2 mm

