




HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

BSN 250 L33-A2-TS 230V 50Hz

Encapsulated electromagnetic copper/iron ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps

Product data

Operating and Electrical	
Input Voltage	230 V
Line Frequency	50 Hz
Input frequency	50 Hz
Wiring	
Connector type	Screw
Mechanical and Housing	
Net Weight (Piece)	2.800 kg
Approval and Application	
Approval marks	CE marking ENEC certificate
CE mark	Yes

Product Data	
Order product name	BSN 250 L33-A2-TS 230V 50Hz
Full product name	BSN 250 L33-A2-TS 230V 50Hz
Full EOC	871869674108500
Order code	913700753126
Material no. (12 NC)	913700753126
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696741085
Numerator – packs per outer box	6
EAN/UPC - Case	8718696741092

HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

Dimensional drawing



Product	A1	A2	B1	C1	D1
BSN 250 L33-A2-TS 230V 50Hz	151 mm	132 mm	81 mm	66 mm	6.2 mm

